





NOTES:

1. SUBSTRATE: UV FUSED SILICA
2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	265
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	12
CLEAR APERTURE	Ø21.00
BEVEL	PROTECTIVE AS NEEDED

**EO**® Edmund Optics®



ALL DIMS IN mm

TITLE

265nm, 10nm FWHM, 25mm DIA. FIRST SURFACE UV BANDPASS FILTER

DWG NO

11993

SHEET 1 OF 1