

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Optical Diffusers](#)

Ground Glass Diffusers



- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Common Specifications

General

Note:

Sandblasted on first surface

Physical & Mechanical Properties

Thickness (mm): 1.60


Optical Properties

Coating: Uncoated

Substrate: Float Glass

Wavelength Range (nm): 350 - 2000

Technical Information



Products

Dia. (mm)	Coating	Dimensions (mm)	Grit	Thickness (mm)	Stock Number	Price	Buy
5.00	Uncoated	-	120	1.60	#83-416	€19,06 Volume Pricing	20+ In Stock
6.00	Uncoated	-	120	1.60	#83-081	€19,06 Volume Pricing	20+ In Stock
10.00	Uncoated	-	120	1.60	#83-082	€19,06 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	120	1.60	#83-083	€19,06 Volume Pricing	20+ In Stock
12.50	Uncoated	-	120	1.60	#83-418	€12,62 Volume Pricing	11 In Stock
-	Uncoated	12.50 x 12.50	120	1.60	#83-084	€19,06 Volume Pricing	Contact Us
15.00	Uncoated	-	120	1.60	#83-379	€21,89 Volume Pricing	20+ In Stock
20.00	Uncoated	-	120	1.60	#83-380	€21,89 Volume Pricing	20+ In Stock
25.00	Uncoated	-	120	1.60	#83-419	€14,16 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	120	1.60	#83-381	€21,89 Volume Pricing	5 In Stock
50.00	Uncoated	-	120	1.60	#83-420	€18,28 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	120	1.60	#83-382	€25,24 Volume Pricing	20+ In Stock
100.00	Uncoated	-	120	1.60	#83-383	€62,32 Volume Pricing	8 In Stock
-	Uncoated	100.00 x 100.00	120	1.60	#83-384	€47,64 Volume Pricing	20+ In Stock
-	Uncoated	150.00 x 150.00	120	1.60	#83-385	€68,50 Volume Pricing	5 In Stock
-	Uncoated	200.00 x 200.00	120	1.60	#83-386	€78,28 Volume Pricing	6 In Stock
-	Uncoated	250.00 x 250.00	120	1.60	#83-387	€101,97 Volume Pricing	20+ In Stock

5.00	Uncoated	-	220	1.60	#62-614	€19,06 Volume Pricing	20+ In Stock
6.00	Uncoated	-	220	1.60	#45-650	€19,06 Volume Pricing	20+ In Stock
10.00	Uncoated	-	220	1.60	#45-651	€19,06 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	220	1.60	#62-615	€19,06 Volume Pricing	20+ In Stock
12.50	Uncoated	-	220	1.60	#62-616	€12,62 Volume Pricing	20+ In Stock
-	Uncoated	12.50 x 12.50	220	1.60	#62-617	€19,06 Volume Pricing	20+ In Stock
15.00	Uncoated	-	220	1.60	#45-652	€21,89 Volume Pricing	20+ In Stock
20.00	Uncoated	-	220	1.60	#62-618	€21,89 Volume Pricing	Contact Us
25.00	Uncoated	-	220	1.60	#45-653	€15,19 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	220	1.60	#45-654	€21,89 Volume Pricing	20+ In Stock
50.00	Uncoated	-	220	1.60	#62-619	€18,28 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	220	1.60	#45-655	€25,24 Volume Pricing	4 In Stock
100.00	Uncoated	-	220	1.60	#62-620	€62,32 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	220	1.60	#45-656	€47,64 Volume Pricing	6 In Stock
-	Uncoated	150.00 x 150.00	220	1.60	#47-951	€68,50 Volume Pricing	12 In Stock
-	Uncoated	200.00 x 200.00	220	1.60	#47-952	€78,28 Volume Pricing	1 In Stock
-	Uncoated	250.00 x 250.00	220	1.60	#47-953	€101,97 Volume Pricing	20+ In Stock
10.00	Uncoated	-	600	1.60	#38-782	€19,06 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	600	1.60	#38-783	€19,06 Volume Pricing	12 In Stock

12.50	Uncoated	-	600	1.60	#38-784	€12,62 Volume Pricing	20+ In Stock
-	Uncoated	12.50 x 12.50	600	1.60	#38-785	€19,06 Volume Pricing	20+ In Stock
25.00	Uncoated	-	600	1.60	#38-786	€15,19 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	600	1.60	#38-787	€21,89 Volume Pricing	7 In Stock
50.00	Uncoated	-	600	1.60	#38-788	€18,28 Volume Pricing	7 In Stock
-	Uncoated	50.00 x 50.00	600	1.60	#38-789	€25,24 Volume Pricing	20+ In Stock
100.00	Uncoated	-	600	1.60	#38-790	€62,32 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	600	1.60	#38-791	€47,64 Volume Pricing	7 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com