

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Mitutoyo Compact Objectives See More by [Mitutoyo](#)



- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Small Size with Excellent Performance
- Long Working Distances
- Easily Integrates with C-Mount Cameras

Common Specifications

General

Manufacturer: Mitutoyo

Physical & Mechanical Properties

Maximum Diameter (mm): 30

Optical Properties

Wavelength Range (nm): 435 - 655

Field Number (mm): 24

Parfocal Length (mm): 110

Immersion Liquid: N/A

Sensor

Maximum Sensor Format: 2/3"

Threading & Mounting

Mounting Threads: M26 x 36 TPI

Environmental & Durability Factors

Operating Temperature (°C): +5 to +35

Operating Humidity: 65±20%

Technical Information

Products

| FL (mm) | Magnification | NA | Type | WD (mm) | Stock Number | Price | Buy |
|------------|---------------|------|-------------------------|------------|-------------------------|---------|----------|
| 58.99 | 1X | 0.03 | Microscope Objective | 73.7 | #56-988 | €492,00 | In Stock |
| 60.33 | 2X | 0.06 | Microscope Objective | 92.0 | #56-989 | €492,00 | 3-4 days |
| 50.61 | 3X | 0.07 | Microscope Objective | 77.8 | #56-990 | €525,00 | 3-4 days |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com