

[All Products](#) / [Laser Optics](#) / [Laser Lenses](#) / [Plano-Convex \(PCX\) Laser Lenses](#)
TECHSPEC®

785nm Laser Line Coated Plano-Convex (PCX) Lenses



- <0.25% Reflection at 785nm
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR-I](#), [NIR-II](#)
- [405nm](#), [532nm](#), [633nm](#), 785nm, [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

Common Specifications

Physical & Mechanical Properties


Bevel:	Protective as needed
--------	----------------------

Optical Properties

Coating:	Laser V-Coat (785nm)
----------	----------------------

Surface Quality:	40-20	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4	Focal Length Tolerance (%):	±1
Design Wavelength DWL (nm):	785	Damage Threshold, By Design:	5 J/cm ² @ 785nm, 10ns

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
5.00	7.50	6.43	Laser V-Coat (785nm)	N-SF11	#89-014	€56,14 Volume Pricing	2 In Stock
5.00	10.00	8.92	Laser V-Coat (785nm)	N-BK7	#89-015	€56,14 Volume Pricing	Contact Us
5.00	12.00	10.83	Laser V-Coat (785nm)	N-BK7	#89-016	€56,14 Volume Pricing	5 In Stock
5.00	15.00	13.94	Laser V-Coat (785nm)	N-BK7	#89-017	€56,14 Volume Pricing	2 In Stock
5.00	20.00	19.02	Laser V-Coat (785nm)	N-BK7	#89-018	€56,14 Volume Pricing	2 In Stock
5.00	25.00	23.95	Laser V-Coat (785nm)	N-BK7	#89-019	€56,14 Volume Pricing	7 In Stock
5.00	30.00	28.95	Laser V-Coat (785nm)	N-BK7	#89-020	€56,14 Volume Pricing	8 In Stock
6.00	6.00	4.60	Laser V-Coat (785nm)	N-SF11	#65-509	€48,41 Volume Pricing	7 In Stock
6.00	7.50	6.1	Laser V-Coat (785nm)	N-SF11	#69-465	€47,90 Volume Pricing	5 In Stock
6.00	9.00	7.95	Laser V-Coat (785nm)	N-SF5	#66-263	€47,90 Volume Pricing	8 In Stock
6.00	12.00	10.94	Laser V-Coat (785nm)	N-BK7	#65-510	€46,35 Volume Pricing	9 In Stock
6.00	15.00	13.68	Laser V-Coat (785nm)	N-BK7	#69-466	€46,35 Volume Pricing	20+ In Stock

6.00	18.00	17.07	Laser V-Coat (785nm)	N-BK7	#65-511	€46,87 Volume Pricing	14 In Stock
6.00	21.00	20.06	Laser V-Coat (785nm)	N-BK7	#69-467	€46,87 Volume Pricing	7 In Stock
6.00	24.00	23.01	Laser V-Coat (785nm)	N-BK7	#65-512	€46,87 Volume Pricing	10 In Stock
6.00	30.00	29.14	Laser V-Coat (785nm)	N-BK7	#65-513	€46,35 Volume Pricing	17 In Stock
6.00	36.00	34.95	Laser V-Coat (785nm)	N-BK7	#69-468	€46,87 Volume Pricing	Contact Us
6.00	48.00	46.96	Laser V-Coat (785nm)	N-BK7	#69-469	€46,87 Volume Pricing	7 In Stock
6.00	60.00	58.96	Laser V-Coat (785nm)	N-BK7	#69-470	€46,87 Volume Pricing	9 In Stock
6.00	72.00	70.97	Laser V-Coat (785nm)	N-BK7	#69-471	€46,87 Volume Pricing	20+ In Stock
9.00	9.00	7.32	Laser V-Coat (785nm)	N-SF11	#65-514	€48,93 Volume Pricing	20+ In Stock
9.00	13.50	11.94	Laser V-Coat (785nm)	N-SF5	#66-264	€48,93 Volume Pricing	20+ In Stock
9.00	12.00	10.60	Laser V-Coat (785nm)	N-SF11	#69-472	€48,93 Volume Pricing	9 In Stock
9.00	15.00	13.02	Laser V-Coat (785nm)	N-BK7	#69-473	€48,93 Volume Pricing	12 In Stock
9.00	18.00	16.41	Laser V-Coat (785nm)	N-BK7	#65-515	€47,90 Volume Pricing	4 In Stock
9.00	22.00	20.73	Laser V-Coat (785nm)	N-BK7	#69-474	€47,90 Volume Pricing	11 In Stock

9.00	27.00	25.34	Laser V-Coat (785nm)	N-BK7	#65-516	€47,90 Volume Pricing	2 In Stock
9.00	36.00	34.48	Laser V-Coat (785nm)	N-BK7	#65-517	€47,90 Volume Pricing	Contact Us
9.00	45.00	43.98	Laser V-Coat (785nm)	N-BK7	#65-518	€47,90 Volume Pricing	5 In Stock
9.00	54.00	52.69	Laser V-Coat (785nm)	N-BK7	#69-475	€47,90 Volume Pricing	11 In Stock
9.00	72.00	70.68	Laser V-Coat (785nm)	N-BK7	#69-476	€47,90 Volume Pricing	7 In Stock
9.00	90.00	88.68	Laser V-Coat (785nm)	N-BK7	#69-477	€47,90 Volume Pricing	7 In Stock
10.00	10.00	8.18	Laser V-Coat (785nm)	N-SF11	#69-478	€48,93 Volume Pricing	20+ In Stock
10.00	15.00	13.32	Laser V-Coat (785nm)	N-SF11	#69-479	€48,93 Volume Pricing	10 In Stock
10.00	20.00	18.03	Laser V-Coat (785nm)	N-BK7	#69-480	€47,90 Volume Pricing	14 In Stock
10.00	25.00	23.02	Laser V-Coat (785nm)	N-BK7	#69-481	€47,90 Volume Pricing	Contact Us
10.00	30.00	28.01	Laser V-Coat (785nm)	N-BK7	#69-482	€47,90 Volume Pricing	5 In Stock
10.00	40.00	38.02	Laser V-Coat (785nm)	N-BK7	#69-483	€47,90 Volume Pricing	14 In Stock
10.00	50.00	48.02	Laser V-Coat (785nm)	N-BK7	#69-484	€47,90 Volume Pricing	14 In Stock
10.00	75.00	73.02	Laser V-Coat (785nm)	N-BK7	#69-485	€47,90 Volume Pricing	5 In Stock

10.00	100.00	98.02	Laser V-Coat (785nm)	N-BK7	#69-486	€47,90 Volume Pricing	15 In Stock
12.00	12.00	9.76	Laser V-Coat (785nm)	N-SF11	#65-519	€50,99 Volume Pricing	4 In Stock
12.00	15.00	12.03	Laser V-Coat (785nm)	N-BK7	#69-487	€50,99 Volume Pricing	20+ In Stock
12.00	18.00	16.22	Laser V-Coat (785nm)	N-SF5	#66-265	€50,99 Volume Pricing	7 In Stock
12.00	20.00	17.69	Laser V-Coat (785nm)	N-BK7	#69-488	€50,99 Volume Pricing	1 In Stock
12.00	24.00	22.15	Laser V-Coat (785nm)	N-BK7	#65-520	€49,96 Volume Pricing	20+ In Stock
12.00	30.00	28.02	Laser V-Coat (785nm)	N-BK7	#69-489	€49,96 Volume Pricing	Contact Us
12.00	42.00	40.22	Laser V-Coat (785nm)	N-BK7	#69-490	€49,96 Volume Pricing	6 In Stock
12.00	48.00	46.36	Laser V-Coat (785nm)	N-BK7	#65-522	€49,96 Volume Pricing	20+ In Stock
12.00	60.00	58.37	Laser V-Coat (785nm)	N-BK7	#65-523	€49,96 Volume Pricing	4 In Stock
12.00	54.00	52.02	Laser V-Coat (785nm)	N-BK7	#69-491	€49,96 Volume Pricing	3 In Stock
12.00	72.00	70.42	Laser V-Coat (785nm)	N-BK7	#69-492	€49,96 Volume Pricing	Contact Us
12.00	84.00	82.39	Laser V-Coat (785nm)	N-BK7	#69-493	€49,96 Volume Pricing	7 In Stock
12.00	100.00	98.25	Laser V-Coat (785nm)	N-BK7	#69-494	€49,96 Volume Pricing	20+ In Stock

15.00	15.00	11.71	Laser V-Coat (785nm)	N-SF5	#87-609	€52,53 Volume Pricing	17 In Stock
15.00	18.00	15.61	Laser V-Coat (785nm)	N-SF5	#87-610	€52,53 Volume Pricing	16 In Stock
15.00	20.00	17.74	Laser V-Coat (785nm)	N-SF5	#87-611	€52,53 Volume Pricing	16 In Stock
15.00	22.50	20.50	Laser V-Coat (785nm)	N-SF5	#87-612	€52,53 Volume Pricing	12 In Stock
20.00	20.00	17.42	Laser V-Coat (785nm)	N-SF11	#89-021	€57,68 Volume Pricing	20+ In Stock
20.00	25.00	22.76	Laser V-Coat (785nm)	N-SF11	#89-022	€57,17 Volume Pricing	9 In Stock
20.00	35.00	32.04	Laser V-Coat (785nm)	N-BK7	#89-023	€57,17 Volume Pricing	14 In Stock
20.00	40.00	36.77	Laser V-Coat (785nm)	N-BK7	#89-024	€55,62 Volume Pricing	4 In Stock
20.00	50.00	47.87	Laser V-Coat (785nm)	N-BK7	#89-025	€55,62 Volume Pricing	8 In Stock
20.00	60.00	57.03	Laser V-Coat (785nm)	N-BK7	#89-026	€55,62 Volume Pricing	5 In Stock
20.00	70.00	68.03	Laser V-Coat (785nm)	N-BK7	#89-027	€55,62 Volume Pricing	5 In Stock
20.00	80.00	78.45	Laser V-Coat (785nm)	N-BK7	#89-028	€55,62 Volume Pricing	6 In Stock
20.00	100.00	97.13	Laser V-Coat (785nm)	N-BK7	#89-029	€55,62 Volume Pricing	7 In Stock
20.00	150.00	148.02	Laser V-Coat (785nm)	N-BK7	#89-030	€55,62 Volume Pricing	20+ In Stock

25.00	25.00	20.22	Laser V-Coat (785nm)	N-SF5	#65-524	€57,68 Volume Pricing	17 In Stock
25.00	30.00	24.69	Laser V-Coat (785nm)	N-BK7	#69-495	€57,68 Volume Pricing	5 In Stock
25.00	35.00	30.42	Laser V-Coat (785nm)	N-BK7	#69-496	€57,68 Volume Pricing	1 In Stock
25.00	40.00	36.31	Laser V-Coat (785nm)	N-BK7	#69-497	€57,68 Volume Pricing	6 In Stock
25.00	50.00	46.75	Laser V-Coat (785nm)	N-BK7	#65-525	€55,62 Volume Pricing	11 In Stock
25.00	60.00	56.90	Laser V-Coat (785nm)	N-BK7	#69-498	€55,62 Volume Pricing	5 In Stock
25.00	75.00	72.00	Laser V-Coat (785nm)	N-BK7	#65-526	€55,62 Volume Pricing	12 In Stock
25.00	85.00	82.17	Laser V-Coat (785nm)	N-BK7	#69-499	€55,62 Volume Pricing	14 In Stock
25.00	100.00	97.17	Laser V-Coat (785nm)	N-BK7	#65-527	€55,62 Volume Pricing	16 In Stock
25.00	125.00	122.70	Laser V-Coat (785nm)	N-BK7	#65-528	€55,62 Volume Pricing	1 In Stock
25.00	150.00	147.81	Laser V-Coat (785nm)	N-BK7	#69-500	€55,62 Volume Pricing	2 In Stock
25.00	175.00	172.85	Laser V-Coat (785nm)	N-BK7	#69-501	€55,62 Volume Pricing	Contact Us
25.00	250.00	248.02	Laser V-Coat (785nm)	N-BK7	#69-502	€55,62 Volume Pricing	2 In Stock
25.00	300.00	298.02	Laser V-Coat (785nm)	N-BK7	#69-503	€55,62 Volume Pricing	12 In Stock

25.00	500.00	497.89	Laser V-Coat (785nm)	N-BK7	#69-504	€55,62 Volume Pricing	Contact Us
25.00	750.00	747.89	Laser V-Coat (785nm)	N-BK7	#69-505	€55,62 Volume Pricing	2 In Stock
30.00	30.00	26.13	Laser V-Coat (785nm)	N-SF11	#26-150	€65,41 Volume Pricing	8 In Stock
30.00	40.00	37.20	Laser V-Coat (785nm)	N-SF11	#26-151	€63,86 Volume Pricing	9 In Stock
30.00	50.00	46.17	Laser V-Coat (785nm)	N-SF5	#26-152	€63,86 Volume Pricing	9 In Stock
30.00	100.00	96.01	Laser V-Coat (785nm)	N-BK7	#26-153	€62,32 Volume Pricing	5 In Stock
30.00	120.00	116.04	Laser V-Coat (785nm)	N-BK7	#26-154	€62,32 Volume Pricing	5 In Stock
40.00	40.00	35.13	Laser V-Coat (785nm)	N-SF11	#26-155	€70,56 Volume Pricing	9 In Stock
40.00	60.00	53.90	Laser V-Coat (785nm)	N-BK7	#26-156	€70,56 Volume Pricing	5 In Stock
40.00	300.00	296.70	Laser V-Coat (785nm)	N-BK7	#26-157	€69,53 Volume Pricing	3 In Stock
40.00	400.00	396.70	Laser V-Coat (785nm)	N-BK7	#26-158	€69,53 Volume Pricing	3 In Stock
50.00	50.00	43.28	Laser V-Coat (785nm)	N-SF11	#69-506	€75,71 Volume Pricing	8 In Stock
50.00	75.00	67.70	Laser V-Coat (785nm)	N-BK7	#69-507	€73,65 Volume Pricing	6 In Stock
50.00	100.00	93.41	Laser V-Coat (785nm)	N-BK7	#69-508	€71,07 Volume Pricing	1 In Stock

50.00	125.00	118.39	Laser V-Coat (785nm)	N-BK7	#69-509	€71,07 Volume Pricing	6 In Stock
50.00	150.00	144.07	Laser V-Coat (785nm)	N-BK7	#69-510	€71,07 Volume Pricing	3 In Stock
50.00	175.00	169.05	Laser V-Coat (785nm)	N-BK7	#69-511	€71,07 Volume Pricing	Contact Us
50.00	200.00	196.66	Laser V-Coat (785nm)	N-BK7	#69-512	€71,07 Volume Pricing	1 In Stock
50.00	250.00	246.74	Laser V-Coat (785nm)	N-BK7	#69-513	€71,07 Volume Pricing	8 In Stock
50.00	500.00	496.70	Laser V-Coat (785nm)	N-BK7	#69-514	€71,07 Volume Pricing	9 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com