

TECHSPEC® 10mm Length, T-Mount Extension Tube



Stock #52-294 3-4 DAYS

⊖ 1 ⊕ €30²⁵

ADD TO CART

Qty 1-4

€30,25

Qty 5+

€27,30

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Extension Tube

Function:
Extension Tube (Fixed)

Physical & Mechanical Properties

Extension Length (mm):
10.0

Total Length (mm):
13.45

Outer Diameter (mm):
48.0

Clear Aperture CA (mm):
37.0

Threading & Mounting

Thread Type:
T-Mount

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

PRODUCT DETAILS

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.
