

## 15.8mm Dia x 71mm FL, Grade 1, Plano-Convex Lens



Stock #74-056 CLEARANCE 3-4 DAYS

⊖ 1 ⊕ €10.<sup>00</sup>

**ADD TO CART**

Qty 1+

€10,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

### SPECIFICATIONS

#### General

Type:  
Plano-Convex Lens

#### Physical & Mechanical Properties

Diameter (mm):  
15.80

## Optical Properties

Effective Focal Length EFL (mm):  
71.00

f#:  
4.49

Numerical Aperture NA:  
0.11

## Regulatory Compliance

RoHS:  
Not Compliant

Certificate of Conformance:  
[View](#)

## PRODUCT DETAILS

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## TECHNICAL INFORMATION

