

19mm Dia x 476mm FL, Grade 1, Plano-Convex Lens



Stock #76-173 CLEARANCE 3-4 DAYS

⊖ 1 ⊕ €10.⁰⁰

ADD TO CART

Qty 1+

€10,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):
19.00

Optical Properties

Effective Focal Length EFL (mm):
476.00

Coating:
Anti-Reflection Coating

f#:
25.05

Numerical Aperture NA:
0.02

Regulatory Compliance

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

TECHNICAL INFORMATION

