

**TECHSPEC® 20mm Travel, Adjustable Length Tube**



Stock #85-513 3-4 DAYS

⊖ 1 ⊕ €76<sup>00</sup>

**ADD TO CART**

Qty 1+  
€76,00

Volume Pricing  
[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**SPECIFICATIONS**

**General**

Function:  
Fixed

**Physical & Mechanical Properties**

**Dimensions (mm):**  
20/25 Dia.

**Overall Length (mm):**  
36.5

**Extension Length (mm):**  
10.0 - 30.0

**Travel (mm):**  
20.0

**Clear Aperture CA (mm):**  
18.0

**Construction:**  
Black Anodized Aluminum

## Threading & Mounting

**Thread Type:**  
M23.2 x 0.75 (Double Male)

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Compliant](#)

## PRODUCT DETAILS

- Enable Adjustment of Cage System Length
- Locking Ring for Easy Length Adjustment
- M23.2 x 0.75 Threading
- Combine with [Thread Adapters](#) to Join Multiple Fixed Extension Tubes

M23.2 Adjustable Length Tubes are designed to connect [M23.2 Fixed Extension Tubes](#) or [Cage System Optical Lens Mounts](#) to construct optical assemblies of varying length. One end of the tube is fixed and has M23.2 x 0.75 male threading, while the other end features a locking ring with male M23.2 x 0.75 threading. The locking ring slides along the length of the tube, enabling the adjustment of the system's length.