


[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris and Aperture Mounts](#)

## Iris Diaphragm Mounts



- Multiple Iris Diameter Options Available
- Durable Anodized Aluminum Construction
- Set Screw Included

## Technical Information



## Products

| Mounting Threads  | Outer Diameter (mm) | Compatible Iris Diameter (mm) | Stock Number            | Price                                    | Buy          |
|-------------------|---------------------|-------------------------------|-------------------------|------------------------------------------|--------------|
| M4 x 0.7 and 8-32 | 26.5                | 10.0                          | <a href="#">#23-118</a> | €46,25<br><a href="#">Volume Pricing</a> | 11 In Stock  |
| M4 x 0.7 and 8-32 | 26.5                | 12.0                          | <a href="#">#23-119</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 39.0                | 14.8                          | <a href="#">#23-120</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 39.0                | 19.8                          | <a href="#">#23-121</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 8-32              | 30.8                | 19.8                          | <a href="#">#53-918</a> | €48,93<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 39.0                | 21.0                          | <a href="#">#23-122</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 8-32              | 32.0                | 21.0                          | <a href="#">#54-862</a> | €52,02<br><a href="#">Volume Pricing</a> | 1 In Stock   |
| M4 x 0.7 and 8-32 | 39.0                | 22.0                          | <a href="#">#23-123</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 39.0                | 24.0                          | <a href="#">#23-124</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 52.0                | 28.0                          | <a href="#">#23-125</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 52.0                | 30.0                          | <a href="#">#23-126</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 52.0                | 33.0                          | <a href="#">#23-127</a> | €47,64<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| M4 x 0.7 and 8-32 | 52.0                | 37.0                          | <a href="#">#23-128</a> | €47,64<br><a href="#">Volume Pricing</a> | 7 In Stock   |
| ¼-20              | 50.8                | 37.0                          | <a href="#">#53-919</a> | €48,93<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| M4 x 0.7 and 8-32 | 52.0                | 38.0                          | <a href="#">#23-129</a> | €47,64<br><a href="#">Volume Pricing</a> | 12 In Stock  |
| ¼-20              | 52.0                | 38.0                          | <a href="#">#54-863</a> | €52,02<br><a href="#">Volume Pricing</a> | 1 In Stock   |

|                        |       |       |                         |                                           |              |
|------------------------|-------|-------|-------------------------|-------------------------------------------|--------------|
| M4 x 0.7 and<br>8-32   | 78.0  | 40.0  | <a href="#">#23-130</a> | €47,64<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| M4 x 0.7 and<br>8-32   | 78.0  | 53.0  | <a href="#">#23-131</a> | €47,64<br><a href="#">Volume Pricing</a>  | 5 In Stock   |
| 1/4-20                 | 66.0  | 53.0  | <a href="#">#53-920</a> | €70,04<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| M4 x 0.7 and<br>8-32   | 78.0  | 54.0  | <a href="#">#23-132</a> | €47,64<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 1/4-20                 | 67.0  | 54.0  | <a href="#">#54-864</a> | €70,04<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| M4 x 0.7 and<br>8-32   | 90.0  | 70.0  | <a href="#">#23-133</a> | €47,64<br><a href="#">Volume Pricing</a>  | 5 In Stock   |
| 1/4-20                 | 86.0  | 70.0  | <a href="#">#53-921</a> | €95,28<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 1/4-20                 | 88.0  | 72.0  | <a href="#">#54-865</a> | €95,28<br><a href="#">Volume Pricing</a>  | 1 In Stock   |
| M6 x 1.0 and<br>1/4-20 | 205.0 | 180.0 | <a href="#">#23-135</a> | €116,39<br><a href="#">Volume Pricing</a> | 6 In Stock   |



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)