

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Filters](#) / [UV-IR Filters](#)

Mounted UV Filters





- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Common Specifications

Optical Properties			
Color:	Clear	Surface Quality:	80-50
Wavelength Range (nm):	350 - 2200	Surface Flatness (P-V):	4 - 6λ
Environmental & Durability Factors			
Operating Temperature (°C):	-15 to +70		

Technical Information



Products

Glass/Filter Number	Cut-On Wavelength (nm)	Thickness (mm)	Wavelength Range (nm)	Filter Thread	Stock Number	Price	Buy
L-39	390.00	2.00	350 - 2200	M22.5 x 0.50	#58-647	€91,67 Volume Pricing	3 In Stock
L-39	390.00	2.00	350 - 2200	M25.5 x 0.50	#46-577	€91,67 Volume Pricing	7 In Stock
L-39	390.00	2.00	350 - 2200	M30.5 x 0.50	#46-576	€99,91 Volume Pricing	20+ In Stock
L-39	390.00	2.00	350 - 2200	M37 x 0.75	#54-039	€59,23 Volume Pricing	8 In Stock
#46-579 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
L-39	390.00	2.00	350 - 2200	M39 x 0.50		€41,15	Contact Us

[#54-725 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

L-39	390.00	2.00	350 - 2200	M40.5 x 0.50		€41,15	14 In Stock
------	--------	------	------------	-----------------	--	--------	-------------

L-39	390.00	2.00	350 - 2200	M43 x 0.75	#54-040	€61,80 Volume Pricing	14 In Stock
------	--------	------	------------	---------------	-------------------------	--	-------------

L-39	390.00	2.00	350 - 2200	M46 x 0.75	#54-041	€61,80 Volume Pricing	14 In Stock
------	--------	------	------------	---------------	-------------------------	--	-------------

L-39	390.00	2.00	350 - 2200	M48 x 0.75	#54-042	€61,80 Volume Pricing	Contact Us
------	--------	------	------------	---------------	-------------------------	--	------------

L-39	390.00	2.00	350 - 2200	M49 x 0.75	#54-043	€61,80 Volume Pricing	20+ In Stock
------	--------	------	------------	---------------	-------------------------	--	--------------

L-39	390.00	2.00	350 - 2200	M52 x 0.75	#54-044	€62,83 Volume Pricing	14 In Stock
------	--------	------	------------	---------------	-------------------------	--	-------------

L-39	390.00	2.00	350 - 2200	M55 x 0.75	#54-045	€62,83 Volume Pricing	20+ In Stock
------	--------	------	------------	---------------	-------------------------	--	--------------

L-39	390.00	2.00	350 - 2200	M58 x 0.75	#54-046	€62,83 Volume Pricing	6 In Stock
------	--------	------	------------	---------------	-------------------------	--	------------

L-39	390.00	2.00	350 - 2200	M62 x 0.75	#54-047	€64,89 Volume Pricing	20+ In Stock
------	--------	------	------------	---------------	-------------------------	--	--------------

#46-578 Clearance



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

Optical
Glass

350.00

2.00

350 - 2200

M67 x
0.75

€44,24

5 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 : www.edmundoptics.com

L-39	390.00	2.00	350 - 2200	M72 x 0.75	#54-048	€64,89 Volume Pricing	20+ In Stock
L-39	390.00	2.00	350 - 2200	M105 x 1.00	#58-648	€448,05 Volume Pricing	1 In Stock