


[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC[®]

Laser Mirror Substrates



- $\lambda/10$ and $\lambda/20$ Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

Common Specifications

Optical Properties			
Surface Quality:	10-5	Coating:	Uncoated
Substrate:	Fused Silica (Corning 7980)		

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Surface Flatness (P-V)	Back Surface	Stock Number	Price	Buy
4.00	-	3.00	λ/10	Commercial Polish	#12-681	€108,15 Volume Pricing	5 In Stock
6.35	-	4.00	λ/10	Commercial Polish	#37-705	€110,21 Volume Pricing	9 In Stock
12.50	-	6.00	λ/10	Ground	#47-017	€82,40 Volume Pricing	20+ In Stock
12.70	-	6.35	λ/10	Commercial Polish	#37-684	€82,40 Volume Pricing	Contact Us
#75-409 New							
							
New							
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
12.70	-	5.00	λ/20	Ground		€82,40	20+ In Stock
12.70	-	6.35	λ/10	Commercial Polish	#21-251	€88,58 Volume Pricing	20+ In Stock
19.10	-	6.35	λ/10	Commercial Polish	#38-000	€94,76 Volume Pricing	20+ In Stock
25.00	-	6.00	λ/10	Ground	#47-018	€100,94 Volume Pricing	20+ In Stock
25.40	-	6.35	λ/10	Commercial Polish	#37-685	€100,94 Volume Pricing	20+ In Stock

[#75-410 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

25.40	-	8.00	Λ/20	Ground		€100,94	20+ In Stock
-------	---	------	------	--------	--	---------	--------------

25.40	-	6.35	Λ/10	Commercial Polish	#21-252	€108,15 Volume Pricing	16 In Stock
-------	---	------	------	-------------------	-------------------------	---	-------------

38.10	-	6.35	Λ/10	Commercial Polish	#38-002	€118,45 Volume Pricing	20+ In Stock
-------	---	------	------	-------------------	-------------------------	---	--------------

38.10	-	9.53	Λ/10	Commercial Polish	#23-898	€114,33 Volume Pricing	3 In Stock
-------	---	------	------	-------------------	-------------------------	---	------------

50.00	-	10.00	Λ/10	Ground	#47-155	€162,74 Volume Pricing	20+ In Stock
-------	---	-------	------	--------	-------------------------	---	--------------

50.80	-	9.53	Λ/10	Commercial Polish	#37-687	€162,74 Volume Pricing	20+ In Stock
-------	---	------	------	-------------------	-------------------------	---	--------------

[#75-417 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

50.80	-	12.50	Λ/20	Ground		€162,74	Contact Us
-------	---	-------	------	--------	--	---------	------------

-	6.35 x 6.35	3.18	$\lambda/10$	Commercial Polish	#37-723	€90,64 Volume Pricing	20+ In Stock
-	9.53 x 6.35	3.18	$\lambda/10$	Commercial Polish	#37-726	€97,85 Volume Pricing	20+ In Stock
-	12.7 x 12.7	6.35	$\lambda/10$	Commercial Polish	#37-724	€104,03 Volume Pricing	20+ In Stock
-	19.1 x 12.7	6.35	$\lambda/10$	Commercial Polish	#37-727	€94,76 Volume Pricing	20+ In Stock
-	25.4 x 25.4	6.35	$\lambda/10$	Commercial Polish	#37-725	€100,94 Volume Pricing	20+ In Stock
-	38.1 x 25.4	6.35	$\lambda/10$	Commercial Polish	#37-728	€154,50 Volume Pricing	20+ In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
 Phone: 1-800-363-1992 :
www.edmundoptics.com