



FOCAL LENGTH (EFL):  $12 \pm 0,12$   
 BACK FOCAL LENGTH (BFL):  $11,23$

- 1 AR COATING: VIS-NIR  
 $R(\text{ABS}) \leq 0,25\%$  AT  $880\text{nm}$  @  $0^\circ$  AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM  $400-870\text{nm}$  @  $0^\circ$  AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM  $890-1000\text{nm}$  @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$10,65 \pm 0,011$ CX	GLASS FUSED SILICA 458/678	R	$10,65 \pm 0,011$ CX
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 6mm Dia, x 12mm FL, VIS-NIR Coated, UV Double-Convex Lens

DWG NO 63819

SHEET SIZE A4  
 SHEET 1 OF 1