

## BG67

Optical properties	
Reflection factor	
$P_d = 0,913$	
Spectral values guaranteed	
$\tau_i$ (450 nm)	$\geq 0,7$
$\tau_i$ (500 nm)	$\geq 0,8$
$\tau_i$ (550 nm)	$\geq 0,65$
$\tau_i$ (600 nm)	$\leq 0,19$
Refractive indices	
$n_F$ (486 nm)	= 1,55
$n_e$ (546 nm)	= 1,54
$n_d$ (587,6 nm)	= 1,54
Sellmeier coefficients	
valid from 400 nm to 1550 nm	
$B_1$	0,7165
$B_2$	0,6218
$B_3$	0,6042
$C_1$	1,764E-09 $\mu\text{m}^2$
$C_2$	1,9422E-02 $\mu\text{m}^2$
$C_3$	100,000 $\mu\text{m}^2$
Internal quality	
Bubble class	2


Mechanical properties	
Reference thickness	
$d = 1,00 \text{ mm}$	
Density	
$\rho = 2,85 \text{ g/cm}^3$	
Knoop hardness	
HK[0.1/20] = 364	

Thermal properties	
Transformation temperature	
$T_g = 390 \text{ }^\circ\text{C}$	
Thermal expansion in $10^{-6}/\text{K}$	
$\alpha$ (-30°C/+70°C)	= 11,8
$\alpha$ (20°C/300°C)	= 13,7


Chemical properties	
Chemical resistance	
FR class	= 1
SR class	= 52.3
AR class	= 3.3
Resistance against humidity	
Robust glass	
see pocket catalogue "Optical Filter Glass 2020", chapter 5.5	

Colormetric properties				
		1 mm	2 mm	3 mm
Illuminant D65	x	0,209	0,176	0,159
	y	0,321	0,317	0,318
	Y	49,7	33,4	24,0
	$\lambda_d$	491 nm	490 nm	491 nm
	$P_e$	0,383	0,508	0,569
Illuminant A	x	0,285	0,222	0,189
	y	0,450	0,456	0,457
	Y	40,9	25,4	17,5
	$\lambda_d$	499 nm	498 nm	498 nm
	$P_e$	0,372	0,519	0,595

Notes	
Ionically colored glass	
Bandpass filter	
NIR cutoff filter	
$\lambda_{50\%}(d=0.145\text{mm}) @ 641 \text{ nm}$	
DIN 58131	
Disclaimer	
All data without tolerances are to be understood to be reference values.	



## BG67



### Internal transmittance $\tau_i$ at reference thickness

The internal transmittance values, tabulated and graphically represented, are reference values only

$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$
200	< 1,0E-05	500	8,231E-01	800	< 1,000E-05	1100	2,071E-05	2200	8,164E-01	3700	2,218E-01
210	< 1,0E-05	510	8,251E-01	810	< 1,000E-05	1110	2,923E-05	2250	8,345E-01	3750	2,392E-01
220	< 1,0E-05	520	8,162E-01	820	< 1,000E-05	1120	3,952E-05	2300	8,488E-01	3800	2,455E-01
230	< 1,0E-05	530	7,899E-01	830	< 1,000E-05	1130	5,505E-05	2350	8,619E-01	3850	2,318E-01
240	< 1,0E-05	540	7,437E-01	840	< 1,000E-05	1140	7,511E-05	2400	8,717E-01	3900	2,036E-01
250	< 1,0E-05	550	6,764E-01	850	< 1,000E-05	1150	1,020E-04	2450	8,803E-01	3950	1,699E-01
260	< 1,0E-05	560	5,876E-01	860	< 1,000E-05	1160	1,362E-04	2500	8,844E-01	4000	1,268E-01
270	< 1,0E-05	570	4,859E-01	870	< 1,000E-05	1170	1,856E-04	2550	8,871E-01	4050	7,709E-02
280	< 1,0E-05	580	3,787E-01	880	< 1,000E-05	1180	2,399E-04	2600	8,867E-01	4100	4,066E-02
290	< 1,0E-05	590	2,747E-01	890	< 1,000E-05	1190	3,271E-04	2650	8,855E-01	4150	2,051E-02
300	< 1,0E-05	600	1,851E-01	900	< 1,000E-05	1200	4,258E-04	2700	8,805E-01	4200	1,109E-02
310	< 1,0E-05	610	1,152E-01	910	< 1,000E-05	1250	1,575E-03	2750	8,647E-01	4250	7,611E-03
320	< 1,000E-05	620	6,630E-02	920	< 1,000E-05	1300	4,935E-03	2800	7,974E-01	4300	7,207E-03
330	1,702E-04	630	3,513E-02	930	< 1,000E-05	1350	1,287E-02	2850	6,825E-01	4350	7,703E-03
340	1,300E-02	640	1,721E-02	940	< 1,000E-05	1400	2,625E-02	2900	5,817E-01	4400	7,300E-03
350	9,108E-02	650	7,798E-03	950	< 1,000E-05	1450	5,320E-02	2950	5,066E-01	4450	6,119E-03
360	2,195E-01	660	3,302E-03	960	< 1,000E-05	1500	9,161E-02	3000	4,476E-01	4500	4,921E-03
370	3,360E-01	670	1,321E-03	970	< 1,000E-05	1550	1,447E-01	3050	3,964E-01	4550	4,292E-03
380	4,226E-01	680	5,023E-04	980	< 1,000E-05	1600	2,069E-01	3100	3,497E-01	4600	4,391E-03
390	4,878E-01	690	1,842E-04	990	< 1,000E-05	1650	2,769E-01	3150	3,079E-01	4650	5,777E-03
400	5,392E-01	700	8,097E-05	1000	< 1,000E-05	1700	3,488E-01	3200	2,721E-01	4700	9,208E-03
410	5,833E-01	710	2,428E-05	1010	< 1,000E-05	1750	4,211E-01	3250	2,426E-01	4750	1,479E-02
420	6,234E-01	720	< 1,000E-05	1020	< 1,000E-05	1800	4,898E-01	3300	2,195E-01	4800	2,212E-02
430	6,594E-01	730	< 1,000E-05	1030	< 1,000E-05	1850	5,517E-01	3350	2,018E-01	4850	3,079E-02
440	6,935E-01	740	< 1,000E-05	1040	< 1,000E-05	1900	6,083E-01	3400	1,895E-01	4900	4,149E-02
450	7,239E-01	750	< 1,000E-05	1050	< 1,000E-05	1950	6,584E-01	3450	1,825E-01	4950	5,501E-02
460	7,523E-01	760	< 1,000E-05	1060	< 1,000E-05	2000	7,010E-01	3500	1,804E-01	5000	7,058E-02
470	7,760E-01	770	< 1,000E-05	1070	< 1,000E-05	2050	7,377E-01	3550	1,834E-01	5050	8,601E-02
480	7,970E-01	780	< 1,000E-05	1080	1,035E-05	2100	7,696E-01	3600	1,913E-01	5100	9,768E-02
490	8,128E-01	790	< 1,000E-05	1090	1,536E-05	2150	7,959E-01	3650	2,044E-01	5150	1,023E-01