




NOTES:

1. SUBSTRATE:  
Zinc Selenide (ZnSe)
2. PARALLELISM:  
SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO <3 ARCMIN
3. COATING:  
S1 & S2: R(AVG) <3.0% @ 2 - 13µm  
R(ABS) <6% @ 2 - 13µm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	$\lambda/20 @ 10.6\mu\text{m}$	$\lambda/20 @ 10.6\mu\text{m}$
CLEAR APERTURE	$\phi 43.18$	$\phi 43.18$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

Edmund Optics®

50.8mm Dia., 5mm Thick, 2-13µm BBAR Coated, ISP Optics Zinc Selenide (ZnSe) Window

TITLE

DWG NO

24676

SHEET 154 OF 175