

[All Products](#) / [Imaging Lenses](#) / [Ruggedized Lenses for Harsh Environments](#)

TECHSPEC® Athermal Imaging Lenses




- Designed to Maintain High Resolution Over a Wide Temperature Range
- Ruggedized for Shock and Vibration Environments
- Large Sensor Coverage up to 1.1"
- Optothermal Stability from [Passive Athermalization](#)
- [2022 Silver VSD Innovators Award Winner](#) and 2022 Inspect Award Winner

Common Specifications

General			
Series:		Athermal Series	
Physical & Mechanical Properties			
Iris Option:		Fixed	
Optical Properties			
Maximum Image Circle (mm):		19.30	Number of Elements (Groups): 7 (3)
Working Distance (mm):		4000 - ∞	
Sensor			
Maximum Sensor Format:		1.2"	
Pixel Size (µm):		2.74	
Threading & Mounting			
Mount:		C-Mount	
Environmental & Durability Factors			
Operating Temperature (°C):		-10 to +50	Type of Ruggedization: Athermal

Technical Information



Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
100.00	1.2"	f/4	4000 - ∞	C- Mount	#16-849	€1.730,00	5 In Stock
100.00	1.2"	f/5.6	4000 - ∞	C- Mount	#16-850	€1.730,00	1 In Stock
100.00	1.2"	f/8	4000 - ∞	C- Mount	#16-851	€1.730,00	2 In Stock
150.00	1.2"	f/4	4000 - ∞	C- Mount	#16-852	€1.730,00	1 In Stock
150.00	1.2"	f/5.6	4000 - ∞	C- Mount	#16-853	€1.730,00	1 In Stock
150.00	1.2"	f/8	4000 - ∞	C- Mount	#16-854	€1.730,00	Contact Us



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com