

[All Products](#) /
 [Laser Optics](#) /
 [Laser Mirrors](#) /
 [Laser Line Mirrors](#)

TECHSPEC® Dual Band Zerodur® Laser Line Mirrors



- >99.5% Reflectivity at Design Wavelengths
- Low Coefficient of Thermal Expansion
- 532/1064nm or 635/670/1064nm Wavelength Bands

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Parallelism (arcsec):	30
Edges:	Ground		

Optical Properties

Substrate:	ZERODUR®		
Coating Type:	Dielectric	Surface Quality:	20-10

Technical Information

Products

DWL (nm)	Dia. (mm)	Thickness (mm)	Stock Number	Price	Buy
532, 1064	10.00	2.00	#29-056	€148,32 Volume Pricing	9 In Stock
532, 1064	15.00	3.00	#29-057	€175,10 Volume Pricing	9 In Stock
532, 1064	20.00	3.00	#29-058	€182,31 Volume Pricing	8 In Stock
532, 1064	25.00	4.00	#29-059	€199,82 Volume Pricing	3 In Stock
532, 1064	40.00	5.00	#29-060	€302,82	5 In Stock
532, 1064	50.00	5.00	#29-061	€371,83 Volume Pricing	5 In Stock
635, 670, 1064	10.00	2.00	#29-062	€148,32 Volume Pricing	9 In Stock
635, 670, 1064	15.00	3.00	#29-063	€175,10 Volume Pricing	9 In Stock
635, 670, 1064	20.00	3.00	#29-064	€182,31 Volume Pricing	9 In Stock
635, 670, 1064	25.00	4.00	#29-065	€199,82 Volume Pricing	20+ In Stock
635, 670, 1064	40.00	5.00	#29-066	€302,82	7 In Stock
635, 670, 1064	50.00	5.00	#29-067	€371,83 Volume Pricing	4 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com