


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Specialty Windows](#)

Infrared (IR) Material Windows



- Excellent Optics for Infrared Detectors
- Minimal Absorption Loss from 8 - 14 μ m
- Easily Cut to Size

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	0.38	Thickness (inches):	0.015
Young's Modulus (GPa):	0.40 - 1.24		

Optical Properties

Coating: Uncoated

Index of Refraction (n_d):	Visible (Sodium D Line): 1.52 8-14 μ m: 1.53 15 μ m+: 1.48	Substrate:	Polymer Film
--	--	-------------------	--------------

Wavelength Range (nm):	8000 - 14000
-------------------------------	--------------

Material Properties


Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):	11 - 13
--	---------

Flexural Modulus (psi):	$(100-260) \times 10^3$	Shore Hardness:	D60-70
--------------------------------	-------------------------	------------------------	--------


Environmental & Durability Factors

Operating Temperature ($^{\circ}\text{C}$):	100 (Max.)
---	------------

Technical Information



IR Windows in the Visible Spectrum



Products

Dimensions (mm)	Thickness (mm)	Thickness (inches)	Coating	Color	Substrate	Stock Number	Price	Buy
152.40 x 152.40	0.38	0.015	Uncoated	White	Polymer Film	#32-807	€29,00 Qty 6+ €26,25	Contact Us
152.40 x 152.40	0.38	0.015	Uncoated	Translucent	Polymer Film	#32-806	€29,00 Qty 6+ €26,25	3-4 days
304.80 x 304.80	0.38	0.015	Uncoated	White	Polymer Film	#32-809	€80,50 Qty 6+ €72,50	3-4 days
304.80 x 304.80	0.38	0.015	Uncoated	Translucent	Polymer Film	#32-808	€80,50 Qty 6+ €72,50	3-4 days
609.60 x 609.60	0.38	0.015	Uncoated	White	Polymer Film	#88-611	€107,00 Qty 6+ €96,00	3-4 days
609.60 x 609.60	0.38	0.015	Uncoated	Translucent	Polymer Film	#88-610	€107,00 Qty 6+ €96,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com