

[All Products](#) / [Optomechanics](#) / [Motorized Translation Stages](#) / [Motorized Rotary Stages](#)

Compact Motorized Rotation Stages



- Compact Footprint and Economic Price Point
- Light-weight Housing with Durable Stage Platform
- Compatible with [TECHSPEC Stages](#)
- Use Power Supply [#21-075](#) to Power Controller [#23-931](#)

Common Specifications

General				
Note:		Controller Required: #23-931		
		Type of Motor:	Stepper Motor	
Physical & Mechanical Properties				
Type of Movement:		Rotary	Guide System:	Ball Bearing
Travel (°):		360	Accuracy (°):	0.03
Backlash (°):		0.2	Construction:	Aluminum, 3D Printed Plastic
Height (mm):		44.7	Load Capacity (kg):	0.5
Repeatability (°):		0.03	Speed (°/s):	240
Weight (kg):		0.25	Table Diameter (mm):	70
Parallelism (°):		0.0083	Min. Incremental Movement (°):	0.02
Optical Properties				
Resolution (µm):			0.02°	
Electrical				
Maximum Operating Current (mA):			500	
Hardware & Interface Connectivity				
Type of Drive:		Gear Transmission	Computer Interface:	USB-C
Environmental & Durability Factors				
Operating Temperature (°C):			10-40	

Technical Information

Products

Table Diameter (mm)	Type	Travel (°)	Stock Number	Price	Buy
70	Metric	360	#23-929	€937,30	4 In Stock
70	English	360	#23-930	€937,30	2 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com