

TECHSPEC® 40 x 57.5mm Enhanced Aluminum, 4-6λ Mirror



Stock #71-413 **NEW** 3-4 DAYS

⊖ 1 ⊕ €41⁰⁰

ADD TO CART

Qty 1-5

€41,00

Qty 6+

€32,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Flat Mirror

Physical & Mechanical Properties

Dimensions (mm):
40.0 x 57.5

Dimensional Tolerance (mm):
±0.25

Clear Aperture CA (mm):
36.00 x 51.75

Edges:
Seamed, 0.5mm Maximum Edge Chip

Thickness (mm):
3.00

Length (mm):
40.00

Width (mm):
57.50

Optical Properties

Surface Flatness (P-V):
4 - 6λ

Substrate: □
Float Glass

Surface Quality:
60-40

Coating Specification:
R_{avg} ≥ 95% @ 450 - 650nm @ 45°

Coating:
Enhanced Aluminum (450-650nm)

Coating Type:
Metal

Wavelength Range (nm):
450 - 650

Damage Threshold, By Design: □
0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)


PRODUCT DETAILS

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- [Contact Us](#) for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

TECHNICAL INFORMATION



COATING CURVES

COMPATIBLE MOUNTS
