

50.8mm Dia. 343nm $\lambda/2$ Quartz Waveplate Zero Order



Stock #16-885 3-4 DAYS

- 1 + €1.640⁰⁰

ADD TO CART

Qty 1+

€1.640,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Crystalline Waveplate

Configuration:
Air Spaced

Physical & Mechanical Properties

Clear Aperture CA (mm):
35.0

Diameter (mm):
50.80 +0.00/-0.25

Thickness (mm):
6.00 +0.00/-0.25

Construction:
Crystalline

Parallelism (arcsec):
<3

Optical Properties

Coating:
Laser V-Coat (343nm)

Design Wavelength DWL (nm):
343

Substrate:
Crystal Quartz

Retardance:
λ/2

Surface Quality:
20-10

Transmitted Wavefront, P-V:
<λ/8 @ 632.8 nm

Retardance Tolerance:
±λ/300

Temperature Coefficient (λ°C):
0.0001

Coating Specification:
R_{abs} < 0.2% @ on each surface

Damage Threshold, By Design:
>10 J/cm² @ 1064 nm, 10ns

Retardance Order:
0

Regulatory Compliance

RoHS 2015:
[Compliant](#)


Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

PRODUCT DETAILS

- Zero Order and Multiple Order Waveplates
- λ/4 and λ/2 Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than ±1% from the design wavelength of the waveplate. For applications with a greater than ±1% deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



TECHNICAL INFORMATION

