



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM

32913
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : 1
 RMS RADIUS : 10.123
 SED RADIUS : 29.577
 SCALE BAR : 100



REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

32913
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 170.9071 μm
 DIFFRACTION LIMITED RANGE: 17.790 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



32913
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

TRANSVERSE RAY FAN PLOT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

32913
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 0.7000 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



www.edmundoptics.com