

SPOT DIAGRAM



49327INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 5.130
GD RADIUS : 14.381
SCALE BAR : 40

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49327INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 277.2152 μm
DIFFRACTION LIMITED RANGE: 30.443 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

49327INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 100.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49327INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM