


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

Protected Aluminum Typical Coating Performance
 $R_{avg} = 85\%$ from 400 -700nm
FOR REFERENCE ONLY



COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

UV-VIS [250-700nm] Anti-Reflection Coating Performance
Typical Energy Density Limit: 3 J/cm² @ 355nm, 10ns; 5 J/cm² @ 532nm, 10ns
FOR REFERENCE ONLY

COATING CURVE

